



	CHAMBER WIDTH	CHAMBER SPACING	CENTER TO CENTER	CHAMBER HEIGHT	MAX END CAP O.D. CONNECTION	MAX SIDE O.D. CONNECTION	MAX TOP O.D. CONNECTION
S29	59" (1499mm)	6.0" (150mm) *7.5" (190mm)	65.0" (1651mm) *66.5" (1690mm)	36" (914mm)	32" (810mm)	18" (450mm)	24" (600mm)
S22	55" (1397mm)	6.0" (150mm)	61.0" (1549mm)	35" (889mm)	30" (760mm)	18" (450mm)	24" (600mm)
C10	39.7" (1008mm)	6.0" (150mm)	45.7" (1161mm)	25" (635mm)	20" (500mm)	12" (300mm)	18" (450mm)
M6	33.6" (853mm)	6.0" (150mm)	39.6" (1006mm)	17.5" (445mm)	14" (350mm)	8" (200mm)	12" (300mm)

\*7.5" (190mm) SPACING OF DISTRIBUTION ROWS IS REQUIRED ONLY WHEN A PERPENDICULAR MAIN HEADER ROW IS USED. IF AN INLINE MAIN HEADER ROW IS USED, THEN MIN SPACING CAN BE 6" (150mm)

**CONCEPTUAL PLAN DISCLAIMER**  
 THIS GENERIC DETAIL DOES NOT ENCOMPASS THE SIZING, FIT, AND APPLICABILITY OF THE TRITON CHAMBER SYSTEM FOR THIS SPECIFIC PROJECT. IT IS THE ULTIMATE RESPONSIBILITY OF THE DESIGN ENGINEER TO ASSURE THAT THE STORMWATER SYSTEM DESIGN IS IN FULL COMPLIANCE WITH ALL APPLICABLE LAWS AND REGULATIONS. TRITON PRODUCTS MUST BE DESIGNED AND INSTALLED IN ACCORDANCE WITH TRITON'S MINIMUM REQUIREMENTS. TRITON STORMWATER SOLUTIONS DOES NOT APPROVE PLANS, SIZING, OR SYSTEM DESIGNS. THE DESIGN ENGINEER IS RESPONSIBLE FOR ALL DESIGN DECISIONS.



7600 EAST GRAND RIVER, STE. 195  
 BRIGHTON, MI 48114  
 PHONE: (810) 222-7652 • FAX: (810) 222-1769  
 WWW.TRITONSWS.COM

# CHAMBER CROSS SECTION INFILTRATION

TRITON - STANDARD DETAILS

REVISED:  
 02-21-20 JWM